Product data sheet

Specifications





Shaft extension, TeSys Control, for V3-V6, distance 300-330mm



V/718

Product availability: Stock - Normally stocked in distribution facility

Price*: 35.60 USD

Main

Range	TeSys
Device Short Name	VZ
Product Or Component Type	Shaft extension
Accessory / Separate Part Category	Locking accessory
Product Compatibility	V4 V6 V5 V3
Quantity Per Set	Set of 1

Complementary

Mechanical Interlocking	Door interlocking function
Back/Door Distance	11.8112.60 in (300320 mm) 12.9913.78 in (330350 mm)
Cross-Section Height	0.31 in (8 mm)
Cross-Section Width	0.31 in (8 mm)
Net Weight	6.00 oz (170 g)

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
Gtin	3389110552218
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.93 in (4.9 cm)
Package 1 Width	3.74 in (9.5 cm)
Package 1 Length	11.34 in (28.8 cm)
Package 1 Weight	5.57 oz (158 g)
Unit Type Of Package 2	S03

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 2	35
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	13.05 lb(US) (5.92 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	280
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	123.15 lb(US) (55.86 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free
⊘	Mercury Free
Ø	Rohs Exemption Information Yes
②	Pvc Free
Ø	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov