

Product data sheet

Characteristics

XACB9124

booted head for pushbutton XAC-B - red - 4 mm,
-40..+70 °C

Price* : 16.40 USD



XACB9124 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

| | |
|---------------------------------|----------------------------------------------------------------------------------|
| Range of product | Harmony XAC |
| Product or component type | Head for push-button |
| Component name | XACB |
| Marking | Unmarked |
| Operator additional information | Booted |
| Operating travel | 0.16 in (4 mm) |
| Cap/Operator or lens colour | Red |
| Product compatibility | XENB.... XENC.... XEND.... XESB2011 XESD2201 XESD2241 XESD2251 |
| Sale per indivisible quantity | 10 |

Complementary

| | |
|----------------|------------------------|
| Product weight | 0.01 lb(US) (0.005 kg) |
|----------------|------------------------|

Environment

| | |
|---------------------------------------|-----------------------------------------------------|
| Standards | EN 60947-5-1 IEC 60947-5-1 CSA C22.2 No 14 |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C) |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Vibration resistance | 15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 100 gn conforming to IEC 60068-2-27 |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to EN 50102 |

Ordering and shipping details

| | |
|----------|------------------------------|
| Category | 22473 - PUSHBUTTON, PENDANTS |
|----------|------------------------------|

| | |
|-----------------------|----------------|
| Discount Schedule | CS2 |
| GTIN | 00785901447115 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.01 |
| Returnability | N |
| Country of origin | FR |

Offer Sustainability

| | |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| ----- Substance 1 | Nickel compounds, which is known to the State of California to cause cancer, and |
| ----- Substance 2 | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|