Product data sheet

Specifications





2 HOLE CONTROLE STATION

XALD02H7SP0205

() Discontinued on: Jan 23, 2021

Main

Range Of Product	Harmony XALD	
Product Or Component Type	Empty control station	
Device Short Name	XALD	
Product Destination	For XB5 Ø 22 mm control and signalling units	
Number Of Cut-Out	2 cut-outs	
Colour Of Base Of Enclosure	Light grey RAL 7035)	
Colour Of Cover	Dark grey RAL 7016)	
Material	Polycarbonate	
Cable Entry	2 knock-outs for cable entry 0.55 in (14 mm) 2 knock-outs for Pg 13 cable gland and ISO M20 0.47 in (12 mm)	
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K	

Complementary

• •		
Assembly Style	For customer assembly	
Number Of Horizontal Rows	1	
Number Of Vertical Rows	2	
Net Weight	0.45 lb(US) (0.205 kg)	
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m	
Mounting Of Block	Front mounting	
-	Rear mounting	
Electrical Composition Code	MR1	
	PR1	
	PF1	
	SF1	
	SF2	
	MF2	
	PF2	
	MF1	
	SR2	
	SR1	
Main Group	2 cut-outs	
Group Of Product	UL-CSA grey	

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Protective Treatment	тн	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	
Nema Degree Of Protection	NEMA 13 NEMA 4X	
Ik Degree Of Protection	IK03 conforming to EN 50102	
Standards	EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-5	
Product Certifications	UL CSA	

Ordering and shipping details

Category	22475-WALL STATIONS
Discount Schedule	CS2
Gtin	3389119414029
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.86 in (9.8 cm)
Package 1 Width	2.76 in (7 cm)
Package 1 Length	4.33 in (11 cm)
Package 1 Weight	0.52 lb(US) (0.237 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information