Product data sheet

Specifications





Protective rear cover, Harmony XAP, for plastron XAPE301, insulated material, without opening, IP 65

XAPE901

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 32.80 USD

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Protective rear cover	
Device Short Name	XAPE	
Product Destination	For front plate XAPE301	
Material	Insulated material	
Cable Entry	Knock-out cable entries	
Product Mounting	Flush mounting	
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010	
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts	

Complementary

Net Weight	0.09 lb(US) (0.04 kg)	
Net Weight	0.09 lb(US) (0.04 kg)	

Environment

Protective Treatment	TC TH
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389110628104
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	2.05 in (5.2 cm)
Package 1 Length	2.36 in (6.0 cm)
Package 1 Weight	1.34 oz (38.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	36
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.92 lb(US) (1.78 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

XAPE901

Dimensions Drawings

Dimensions and Mounting



P Usable depth

b		Р	
mm	in.	mm	in.
52	2.05	82.5	3.25