# **Product data sheet**

Specifications





die-cast empty control station, XAPG, grey, Ø 22, 80x80mm front plate, 2 cut-outs

XAPG1202

! Discontinued on: Oct 20, 2020



#### Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPG	
Product Destination	For Ø 22 mm control and signalling units	
Product Front Plate Size	80 x 80 mm	
Usable Depth	1.93 in (49 mm)	
Number Of Cut-Out	2 cut-outs	
Colour Of Base Of Enclosure	Grey RAL 7032)	
Colour Of Cover	Grey RAL 7032)	
Material	Zinc alloy	
Product Mounting	Flush mounting	
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010	

### Complementary

Number Of Vertical Rows	2	
Cable Entry	0.55 in (14 mm) 1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland	
Net Weight	0.99 lb(US) (0.45 kg)	
Compatibility Code	XAPG	_

#### **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class I IEC 60536

#### Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)	
Discount Schedule	CS2	
Gtin	3380110800540	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 24, 2024 Life Is On Schneider 1

Poturnahility	No		

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov