

XUSLNG5D1050R

safety light curtain receiver type 2 - XUSLN -
height 1050 mm - manual start

Price* : 1,528.00 USD



⚠ Discontinued

XUSLNG5D1050R has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtains receiver type 2
Device short name	XUSLN
Product compatibility	XUSLNG5D1050
Design	Compact slim
Output type	1 alarm output PNP 2 safety outputs OSSD solid-state PNP (NO) (short-circuit protection)
Product specific application	For hand protection
Minimum object diameter for detection	1.18 in (30 mm)
[Sn] nominal sensing distance	0.98...49.21 ft (0.3...15 m)
Type of start	Manual
Height protected	41.34 in (1050 mm)
Number of beams	49

Complementary

Detection system	Transmitter-receiver system
Response time	20 ms
[EAA] effective aperture angle	5 ° at 3 m
[Us] rated supply voltage	24 V DC (+/- 20 %) against reverse polarity
[Ie] rated operational current	2 A
Current consumption	90 mA no-load 1.09 A with maximum load
Output current limits	500 mA
Output voltage	24 V
Output circuit type	DC
Local signalling	4 LEDs stop, run, top alignment, bottom alignment
Electrical connection	1 male connector M12 5 pins
Marking	CE
Material	Casing : aluminium End caps : 30 % fibre glass impregnated nylon Front face : acrylic
Fixing mode	End brackets

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61496-1 Machinery directive 2006/42/EC IEC 61496-2 (type 2 ESPE) Work equipment directive 2009/104/EC EMC 2004/108/EC
Product certifications	CSA UL TÜV
Ambient air temperature for operation	32...131 °F (0...55 °C)
Ambient air temperature for storage	-13...167 °F (-25...75 °C)
Relative humidity	0...95 % without condensation
IP degree of protection	IP65
Shock resistance	10 gn 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

Ordering and shipping details

Category	22455 - LIGHT CURTAINS - XUSL
Discount Schedule	DS2
Nbr. of units in pkg.	1
Package weight(Lbs)	8
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0745 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------