Product data sheet

Specifications





Complete beacon, Harmony XVB, indicating 250V 10W + options, blue

XVBL36

Product availability: Stock - Normally stocked in distribution facility

Price*: 114.00 USD

Main

| Range Of Product | Harmony XVB Universal |
|---------------------------------------|--|
| Product Or Component Type | Complete beacon |
| Beacon Or Indicator Bank Unit Type | Base unit direct or tube fixing Illuminated unit |
| Signalling Type | Steady |
| Mounting Diameter | 2.76 in (70 mm) |
| Component Name | XVBL |
| Material | Glass reinforced polyamide: base unit Polycarbonate: illuminated unit |
| Light Source | Bulb not included, blue |
| Bulb Type | Incandescent BA 15d Protected LED |
| [Us] Rated Supply Voltage | <= 250 V |
| Mauimum Bauran Diasinatian In W | 7.14 |

Maximum Power Dissipation In W $~~7~{\rm W}$

Complementary

| · · · · · · · · · · · · · · · · · · · | |
|---|--|
| Connections - Terminals | Screw clamp terminals, <= 1 x 1.5 mm ² with cable end |
| [Ui] Rated Insulation Voltage | 250 V IEC 60947-1 |
| Nominal Voltage Limit | 0.851.1 Un IEC 60947-5-1 |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV IEC 60947-1 |
| Cad Overall Width | 2.76 in (70 mm) |
| Cad Overall Height | 5.47 in (139 mm) |
| Cad Overall Depth | 2.76 in (70 mm) |
| Terminals Description Iso N°1 | (COM-1)PW (GND)GROUND |
| Net Weight | 0.57 lb(US) (0.26 kg) |

Environment

| Pollution Degree | 2 | |
|------------------------|-----------------|--|
| Product Certifications | CCC | |
| | EAC | |
| | CSA C22-2 No 14 | |
| | UL 508 | |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Standards | IEC 60947-5-1 | |
|--|--|--|
| Protective Treatment | TC | |
| Ambient Air Temperature For Operation | -13122 °F (-2550 °C) LED -13158 °F (-2570 °C) incandescent | |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) | |
| Electrical Shock Protection Class | Class I on support tube IEC 61140 Class II on base unit IEC 61140 | |
| Ip Degree Of Protection | IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529 | |
| Nema Degree Of Protection | Type 4X UL indoor) | |

Ordering and shipping details

| Category | US100XV22611 | |
|-------------------|---------------|--|
| Discount Schedule | 00XV | |
| Gtin | 3389110844153 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.23 in (8.2 cm) |
| Package 1 Width | 5.91 in (15.0 cm) |
| Package 1 Length | 3.23 in (8.2 cm) |
| Package 1 Weight | 9.38 oz (266.0 g) |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 18 |
| Package 2 Height | 11.81 in (30.0 cm) |
| Package 2 Width | 11.81 in (30.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 11.47 lb(US) (5.201 kg) |
| | |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes


Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Product data sheet

Connections and Schema

Illuminated Beacon

Wiring Diagram

