Product data sheet

Specifications





Selector switch, Harmony XAC, plastic, black, 2 positions, left/right withdrawal position, stay put

ZA2BG4

Product availability: Stock - Normally stocked in distribution facility

Price*: 112.00 USD

Main

Range Of Product	Harmony XAC
Product Or Component Type	Selector switch
Component Name	ZA2
Product Compatibility	XACA

Complementary

0.09 lb(US) (0.042 kg)
Black
Unmarked
Base of enclosure Front of enclosure

Sale Per Indivisible Quantity

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 UL 508 IEC 60204-32
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
Gtin	3389110645323
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	2.36 in (6.0 cm)
Package 1 Weight	1.73 oz (49.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.36 in (6.0 cm)
Package 2 Width	9.45 in (24.0 cm)
Package 2 Length	7.09 in (18.0 cm)
Package 2 Weight	17.53 oz (497.0 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	6.15 lb(US) (2.788 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov