

Product data sheet

Specifications



Harmony eXLhoist, standard, Connector plug female with cable 3m for ZARB12H

ZARC12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 564.00 USD

Main

Range Of Product	Harmony eXLhoist
Accessory / Separate Part Type	Pre-wired connector
Accessory / Separate Part Category	Connection accessory

Complementary

Product Compatibility	Control station ZARB
Pin Number	62
Total Number Of Wires	48
Cable Composition	8 x 2.8 mm ² + 40 x 1.5 mm ²
Cable Length	9.84 ft (3 m)
Material	PE (polyethylene)
Net Weight	7.94 lb(US) (3.6 kg)

Environment

Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...140 °F (-40...60 °C)
Ip Degree Of Protection	IP65
Nema Degree Of Protection	NEMA 4

Ordering and shipping details

Category	US10CS222479
Discount Schedule	0CS2
Gtin	3606480662379
Returnability	No
Country Of Origin	PL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	11.42 in (29.000 cm)
Package 1 Length	15.35 in (39.000 cm)
Package 1 Weight	6.68 lb(US) (3.030 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	14.15 lb(US) (6.418 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov