# Product data sheet

Specifications



# Round guard for 40mm Emergency stop, Harmony XB4, plastic, yellow, 63.5mm

ZB4BZ1905

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 27.35 USD

#### Main

| Range Of Product                         | Harmony XB4<br>Harmony XB5         |  |
|--|------------------------------------|--|
| Product Or Component Type                | Guard                              |  |
| Accessory / Separate Part<br>Category    | Protection accessory               |  |
| Accessory / Separate Part<br>Destination | Ø 40 mm emergency stop push-button |  |
| Color                                    | Yellow                             |  |
| Quantity Per Set                         | Set of 1                           |  |

## Complementary

| Material   | Plastic                |
|------------|------------------------|
| Net Weight | 0.09 lb(US) (0.042 kg) |

#### Environment

| Ambient Air Temperature For<br>Storage   | -40185 °F (-4085 °C) |
|--|----------------------|
| Ambient Air Temperature For<br>Operation | -40158 °F (-4070 °C) |
| Ik Degree Of Protection                  | IK05                 |

## Ordering and shipping details

| Category          | US10CS222469 |
|-------------------|--------------|
| Discount Schedule | 0CS2         |
| Gtin              | 785901230687 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

## **Packing Units**

| Unit Type Of Package 1       | PCE               |
|------------------------------|-------------------|
| Number Of Units In Package 1 | 1                 |
| Package 1 Height             | 1.50 in (3.8 cm)  |
| Package 1 Width              | 5.51 in (14.0 cm) |
| Package 1 Length             | 7.99 in (20.3 cm) |
| Package 1 Weight             | 1.44 oz (40.8 g)  |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Unit Type Of Package 2       | S02                   |
|------------------------------|-----------------------|
| Number Of Units In Package 2 | 20                    |
| Package 2 Height             | 5.91 in (15.0 cm)     |
| Package 2 Width              | 11.81 in (30.0 cm)    |
| Package 2 Length             | 15.75 in (40.0 cm)    |
| Package 2 Weight             | 2.58 lb(US) (1.17 kg) |

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration   |
| China Rohs Regulation     | China RoHS declaration  |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | End of Life Information   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |