

Product data sheet

Specifications



Blanking plug, Harmony XB5, plastic, black, for 22mm hole

ZB5SZ3

Product availability: Stock - Normally stocked in distribution facility

Price*: 11.00 USD

Main

Range Of Product	Harmony XB5 Harmony XB4
Accessory / Separate Part Type	Blanking plug
Accessory / Separate Part Category	Installation accessories
Product Or Component Type	Blanking plug
Accessory / Separate Part Destination	Ø 22 mm cut-outs for circular heads
Cap/Operator Or Lens Colour	Dark grey

Complementary

Material	Plastic
Bezel Material	Dark grey plastic
Head Type	Standard
Colour	Dark grey
Device Composition	Nut Blanking plug
Sale Per Indivisible Quantity	10
Net Weight	0.02 lb(US) (0.009 kg)
Shape Of Signaling Unit Head	Round
Operator Profile	Flush
Station Name	XALD 2...5 cut-outs XALK 2...5 cut-outs

Environment

Nema Degree Of Protection	NEMA 13 NEMA 4X
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K
Ik Degree Of Protection	IK03 conforming to IEC 50102
Standards	JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-5-4 UL 508 JIS C8201-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
Gtin	3389110099522
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.91 in (2.3 cm)
Package 1 Width	1.10 in (2.8 cm)
Package 1 Length	1.10 in (2.8 cm)
Package 1 Weight	0.28 oz (8 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.76 in (7 cm)
Package 2 Width	2.76 in (7 cm)
Package 2 Length	3.46 in (8.8 cm)
Package 2 Weight	3.42 oz (97 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	400
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	9.63 lb(US) (4.368 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Pro-active compliance \(Product out of EU RoHS legal scope\)](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

California Proposition 65 [WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate \(DIDP\), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov](#)