

# ZCE1A

limit switch head ZCE - metal end plunger with silicone boot

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 11.80 USD



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKD XCKP XCKT XCMD
Associated body	ZCD21 ZCD21M12 ZCD25 ZCD26 ZCD27 ZCD28 ZCD29 ZCD29M12 ZCD31 ZCD35 ZCD37 ZCD39 ZCMD21C12 ZCMD21L08R12 ZCMD21L08U78 ZCMD21L1 ZCMD21L2 ZCMD21L5 ZCMD21M12 ZCMD25L1 ZCMD25L2 ZCMD25L5 ZCMD29C12 ZCMD29L1 ZCMD29L2 ZCMD29L5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD37L1  
 ZCMD37L2  
 ZCMD37L5  
 ZCMD39L1  
 ZCMD39L2  
 ZCMD39L5  
 ZCMD41L1  
 ZCMD41L2  
 ZCMD41L5  
 ZCMD61C12  
 ZCMD61M12  
 ZCMD69C12  
 ZCMD81L1  
 ZCMD81L2  
 ZCMD81L5  
 ZCP21  
 ZCP21M12  
 ZCP25  
 ZCP26  
 ZCP27  
 ZCP28  
 ZCP29  
 ZCP29M12  
 ZCP31  
 ZCP35  
 ZCP37  
 ZCP39  
 ZCT21G11  
 ZCT21N12  
 ZCT21P16  
 ZCT25G11  
 ZCT25N12  
 ZCT25P16  
 ZCT26G11  
 ZCT26N12  
 ZCT26P16  
 ZCT27G11  
 ZCT27N12  
 ZCT27P16  
 ZCT28G11  
 ZCT28N12  
 ZCT28P16

Movement of operating head	Linear
Type of operator	End plunger spring return metal (with silicone boot)
Type of approach	Vertical approach 1 direction

### Complementary

Positive opening	With
------------------	------

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	003389118205307
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	ID

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------