

Product data sheet


Characteristics

10286

Multi 9 - comb busbar - 2L - 18 mm pitch - 12 modules - 100A

Product availability : Stock - Normally stocked in distribution facility

Price* : 69.00 USD



Main

Range	Multi 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	2L
Length in 18 mm modules	12

Complementary

Number of ways	6 ways 2 L
Poles configuration for 1 way	1 x 2P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	36 mm
Marking	L1 L2
Insulation	Insulated
Device presentation	Uncuttable
[Ie] rated operational current	100 A (40 °C)
System Voltage	277 V AC Ph/N 480 V AC Ph/Ph
[Ui] rated insulation voltage	690 V AC
[Uimp] rated impulse withstand voltage	12 kV
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	8.5 in (216 mm)
Colour	Light grey (RAL 7035)
Range compatibility	Multi 9 C60SP

Environment

Standards	UL 1077 IEC 60947-2
-----------	------------------------

GB 14048.2

Fire resistance	1760 °F (960 °C) (30 s)
-----------------	---------------------------

Ordering and shipping details

Category	00908 - C60N SUPPLEMENTARY PROTECTORS
Discount Schedule	DE2
GTIN	00785901846857
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20999999999999999
Returnability	Y
Country of origin	DE

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0726 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
