Product data sheet





analog output module Modicon Quantum - 8 O

140ACO13000C

Discontinued on: Mar 15, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

(!) Discontinued

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Analogue output module

Complementary

J	
Analogue Output Number	8
Addressing Requirement	8 output words
Loop Voltage	630 V DC
Maximum Voltage Drop	<30 V 25 mA
Analogue Output Range	020 mA 020000 counts 025 mA 025000 counts 420 mA 016000 counts 420 mA 04095 counts
Absolute Accuracy Error	+/- 0.2 % of full scale 77 °F (25 °C)
Linearity	+/- 12 μA 420 mA 04095 counts +/- 4 μA 020 mA 020000 counts +/- 4 μA 025 mA 025000 counts +/- 4 μA 420 mA 016000 counts
Accuracy Drift According To Temperature	0.004 % of full scale/°C typical 0.007 % of full scale/°C maximum
Isolation Between Channels And Bus	1780 V for 1 minute AC
Update Time	5 ms
Setting Time	1.6 ms to 5% of the final value 3.2 ms to +/-0.1% of the final value
Fault Type	Open circuit 420 mA
Bus Current Requirement	550 mA
Maximum Power Dissipation In W	5 W
External Power Requirement	630 V
Marking	CE
Local Signalling	for bus communication is present (Active) 1 LED (green) for external fault 1 LED (red) for channel is turned on 8 LEDs (green) for channel fault 8 LEDs (red)
Module Format	Standard
Net Weight	0.66 lb(US) (0.3 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Protective Treatment	Conformal coating Humiseal 1A33	
Product Certifications	cUL FM Class 1 Division 2	
Standards	CSA C22.2 No 142 UL 508	
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 802000 MHz IEC 801-3	
Ambient Air Temperature For Operation	32140 °F (060 °C)	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Relative Humidity	95 % without condensation	
Operating Altitude	<= 16404.2 ft (5000 m)	

Ordering and shipping details

Category	US1PC2118155
Discount Schedule	PC21
Gtin	3595861148024
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.5 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	12.20 in (31.0 cm)
Package 1 Weight	16.97 oz (481.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.42 lb(US) (3.367 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

High Density Analog Output Module (8-Channel)

Wiring Diagram



N/C Not Connected

All terminals labeled "RETURN" are common inside the module.