


Product data sheet

Specifications

Multi9 - comb busbar - 2L - 18 mm pitch - 12 modules - 100A



10286

Product availability: Stock - Normally stocked in distribution facility

Price*: 69.00 USD

Main

Range	Multi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	2L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	6 ways 2 L
Poles Configuration For 1 Way	1 x 2P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	1.42 in (36 mm)
Marking	L1 L2
Insulation	Insulated
Device Presentation	Uncuttable
[Ie] Rated Operational Current	100 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	277 V AC Ph/N 480 V AC Ph/Ph
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	12 kV
Mounting Location	Top tunnel type terminals
9 Mm Pitches	24
Width	8.50 in (216 mm)
Color	Light gray RAL 7035)
Range Compatibility	Multi9 Multi9 C60SP

Environment

Standards	IEC 60947-2 GB 14048.2 UL 1077
Fire Resistance	1760 °F (960 °C) 30 s)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
Gtin	3303430102861
Returnability	Yes
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.51 in (1.300 cm)
Package 1 Width	2.17 in (5.500 cm)
Package 1 Length	8.46 in (21.500 cm)
Package 1 Weight	3.32 oz (94.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	72
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	15.15 lb(US) (6.873 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	