



Price* : 18,226.00 USD



140CPU43412A has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range of product	Modicon Quantum automation platform
Product or component type	Processor
Software name	Concept ProWORX 32
Processor name	80486
Mathematical coprocessor	With

Complementary

Clock frequency	66 MHz
Memory description	Internal RAM 896 kB
Exact time for 1 Kinstruction	0.1...0.5 ms LL984
Watchdog timer	250 ms
Clock drift	+/-8 s/day at 32...140 °F (0...60 °C)
I/O words	30 I/32 O distributed 64 I/64 O max local 64 I/64 O remote
I/O words/network	500 I/500 O distributed
Drops/Network	63 distributed
Number of drops	31 remote
Number of network	2 remote 3 distributed
Battery type	Lithium 7 μ A 210 μ A
Battery capacity	1.2 Ah
Battery life	10 yr
Number of port	1 Modbus Plus 2 Modbus RS232
Communication module processor capacity	6 NOM, NOE, CR, NMS
Switch function	Key switch

Marking	CE
Bus current requirement	1250 mA
Module format	Standard
Product weight	1.87 lb(US) (0.85 kg)

Environment

Product certifications	CUL FM Class 1 Division 2
Standards	CSA C22.2 No 142 UL 508
Resistance to electrostatic discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) 80...2000 MHz conforming to IEC 801-3
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	95 % without condensation
Operating altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	18150 - QUANTUM CONTROLLERS,HSBY,COMM.
Discount Schedule	PC21
GTIN	00785901401841
Nbr. of units in pkg.	1
Package weight(Lbs)	1.3500000000000001
Returnability	N
Country of origin	FR

Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0945 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots