

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,118.30 USD



Main

Range of product	Modicon Quantum automation platform
Product or component type	Dc discrete output module
Discrete output number	32

Complementary

Group of channels	4 groups of 8
Discrete output logic	Positive logic (source)
Addressing requirement	2 output words
Discrete output voltage	24 V DC
Output voltage limits	19.2...30 V
Absolute maximum output	50 V for 1 s decaying pulse
Voltage drop	0.4 V 0.5 A
Maximum load current	16 A per module 4 A per group
Surge current	<= 2 A <= 2 A
Response time	<= 0.1 ms at state 1 to state 0 <= 1 ms at state 0 to state 1
Leakage current	<= 1 mA 24 V
Load inductance	Inductance(H) = 0.5/((current(A)) ² x (switching frequency(Hz))) Inductance(H) = 0.5/((current(A)) ² x (switching frequency(Hz)))
Fault indication	Blown fuse Loss of field power
Associated fuse rating	3 A each point 3 A each point 5 A per group 5 A per group
Isolation between channels and bus	1780 Vrms DC for 1 minute

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Isolation between group	500 Vrms DC for 1 minute
Protection type	Internal output protection by 5 A fuse per group
Power dissipation	5 W
Marking	CE
Local signalling	1 LED green bus communication is present (Active) 1 LED red external fault detected (F) 32 LEDs green input status
Bus current requirement	<= 330 mA <= 330 mA
Module format	Standard
Product weight	0.99 lb(US) (0.45 kg)


Environment

Protective treatment	Conformal coating Humiseal 1A33
Product certifications	C-Tick FM Class 1 Division 2 GOST RMRS
Standards	CSA C22.2 No 142 UL 508
Resistance to electrostatic discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) 80...2000 MHz conforming to IEC 801-3
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	95 % without condensation
Operating altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	18155 - QUANTUM I/O & POWER SUPPLIES
Discount Schedule	PC21
GTIN	003595862015325
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	CN

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

24 Vdc Discrete Output Source Module

Wiring Diagram

