Product data sheet

Specifications





(!) Discontinued - Service only

discrete output module Modicon Quantum - 32 O - negative logic (sink)

140DDO35310

! Discontinued on: Dec 31, 2022

! To be end-of-service on: Dec 31, 2030

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Dc discrete output module
Discrete Output Number	32

Complementary

Group Of Channels	4 groups of 8
Discrete Output Logic	Negative logic (sink)
Addressing Requirement	2 output words
Discrete Output Voltage	24 V DC
Output Voltage Limits	19.230 V
Absolute Maximum Output	50 V 1 s decaying pulse
Maximum Voltage Drop	<0.4 V 0.5 A
Maximum Load Current	16 A per module 4 A per group
Surge Current	5 A 1 ms
Response Time	<= 1 ms at state 0 to state 1 <= 1 ms at state 1 to state 0
Maximum Leakage Current	0.4 mA 30 V
Load Inductance	Inductance(H) = 0.5/((current(A)) ² x (switching frequency(Hz)))
Maximum Tungsten Load	12 W 24 V
Fault Indication	Loss of field power Blown fuse
Associated Fuse Rating	3 A each point 5 A per group
Isolation Between Channels And Bus	1780 Vrms DC for 1 minute
Isolation Between Group	500 Vrms DC for 1 minute
Protection Type	Internal output protection by 5 A fuse per group
Power Dissipation	2.0 W + (0.4 V x total load current)
Marking	CE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Local Signalling	for bus communication is present (Active) 1 LED (green) for external fault detected (F) 1 LED (red) for input status 32 LEDs (green)
Bus Current Requirement	330 mA
Module Format	Standard
Net Weight	0.99 lb(US) (0.45 kg)

Environment

Product Certifications	FM Class 1 Division 2 RINA GOST C-tick RMRS
Standards	UL 508 CSA C22.2 No 142
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 802000 MHz IEC 801-3
Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 16404.2 ft (5000 m)

Ordering and shipping details

Category	US1PC2118155
Discount Schedule	PC21
Gtin	3595861135673
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.42 in (16.3 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	12.28 in (31.2 cm)
Package 1 Weight	17.14 oz (486.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.56 lb(US) (3.882 kg)

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

24 Vdc Discrete Output Sink Module

Wiring Diagram

