

Product data sheet

Characteristics

1S82F

TRANSFORMER DRY 1PH 1KVA

240X480V-24/48V

Product availability : Stock - Normally stocked in distribution facility



Price* : 948.00 USD



Main

Product	Buck and Boost Transformer
Enclosure Code	7A
Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Primary Voltage	240 x 480 V
Power Rating	1 kVA
Secondary Voltage	24/48 V
Temperature Rise	115 °C

Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901796855
Nbr. of units in pkg.	1
Package weight(Lbs)	21.199999999999999
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------