

Product availability : Stock - Normally stocked in distribution facility



Price* : 4,577.00 USD



Main

Range of product	Modicon Quantum automation platform
Product or component type	DIO head-end adaptor

Complementary

Product compatibility	140CRA21210 140CRA21220
Number of port	1 Modbus RS232 twisted pair redundant copper 2 Modbus Plus RS485 twisted pair redundant copper
Transmission rate	1 Mbit/s
I/O words	30 I/32 O
Checks	Checksum Processor RAM RAM address
Power dissipation in W	4 W
Bus current requirement	780 mA

Environment

Resistance to electrostatic discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) 80...2000 MHz conforming to IEC 801-3
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	95 % without condensation
Operating altitude	<= 16404.2 ft (5000 m)
Standards	UL 508
Product certifications	CSA C-Tick

DNV
FM Class 1 Division 2
GL
GOST
RINA
RMRS

Ordering and shipping details

Category	18150 - QUANTUM CONTROLLERS,HSBY,COMM.
Discount Schedule	PC21
GTIN	00785901794721
Nbr. of units in pkg.	1
Package weight(Lbs)	1.1000000000000001
Returnability	Y
Country of origin	FR

Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots