

# Product data sheet

## Characteristics


# 2510KS3

Manual Switch - SS Flush - 2P - Key Operated - No Indicator - 600VAC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 99.86 USD



⚠ Discontinued

2510KS3 has not been replaced. Please contact your customer care center for more information.

### Main

Product	Single Unit Manual Switch
Type	K

### Complementary

Line Rated Current	30 A
Horsepower Rating	3 hp at 460 V AC 2 hp at 230 V AC 2 hp at 115 V AC 3 hp at 575 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC
System Voltage	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Key
Phase	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 (copper)
Height	4.5 in
Width	2.75 in
Depth	2.5 in

### Environment

Certifications	CE UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
----------------	---

NEMA Enclosure Rating	Not rated (flush plate) stainless steel standard size
-----------------------	---

**Ordering and shipping details**

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901077732
Nbr. of units in pkg.	1
Package weight(Lbs)	0.46000000000000002
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------