# Product data sheet

Specifications





## auxiliary contact - 1 SD - 380..415 V - 6 A - for C60

26927

#### () Discontinued on: Jun 30, 2021

#### Main

| mann                        |   |
|-----------------------------|---|
| Range Of Product            | Multi9  |
| Product Or Component Type   | Fault contact   |
| Device Short Name           | SD  |
| Signal Contacts Composition | 1 C/O   |
| Line Rated Current          | AC-12 3 A at 380415 V, AC 50/60 Hz<br>AC-12 6 A at 220240 V, AC 50/60 Hz<br>DC-12 1 A at 130 V, DC<br>DC-12 1.5 A at 60 V, DC<br>DC-12 2 A at 48 V, DC<br>DC-12 6 A at 24 V, DC |
| 9 Mm Pitches                | 1   |

## Complementary

| Mounting Mode           | Fixed  |  |
|-------------------------|--|--|
| Mounting Support        | DIN rail   |  |
| Height                  | 3.31 in (84 mm)  |  |
| Width                   | 0.35 in (9 mm)   |  |
| Depth                   | 2.87 in (73 mm)  |  |
| Connections - Terminals | Clamp terminal2 0.00 in² (1.5 mm²) - flexible<br>Clamp terminal2 0.00 in² (1.5 mm²) - rigid<br>Clamp terminal1 0.000.00 in² (0.52.5 mm²) - flexible<br>Clamp terminal1 0.000.00 in² (0.52.5 mm²) - rigid |  |
| Wire Stripping Length   | 0.35 in (9 mm)   |  |
| Tightening Torque       | 8.85 lbf.in (1 N.m)  |  |

#### Environment

| Standards                                | EN/IEC 60947-5-1                    |
|--|-------------------------------------|
| Product Certifications                   | ASTA<br>KEMA<br>ASEFA<br>LCIE       |
| Ip Degree Of Protection                  | IP20 conforming to EN/IEC 60947-5-1 |
| Pollution Degree                         | 3 EN/IEC 60947-5-1                  |
| Tropicalisation                          | 2 EN/IEC 60947-5-1                  |
| Relative Humidity                        | 95 % 131 °F (55 °C)                 |
| Ambient Air Temperature For<br>Operation | -13122 °F (-2550 °C)                |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ambient Air Temperature For -40...185 °F (-40...85 °C) Storage

## Ordering and shipping details

| Category          | 01078-DE2 MISC |
|-------------------|----------------|
| Discount Schedule | DE2            |
| Gtin              | 3303430269274  |
| Returnability     | No             |
| Country Of Origin | BE             |

#### **Packing Units**

| •                            |                  |
|------------------------------|------------------|
| Unit Type Of Package 1       | PCE              |
| Number Of Units In Package 1 | 1                |
| Package 1 Height             | 0.87 in (2.2 cm) |
| Package 1 Width              | 3.15 in (8 cm)   |
| Package 1 Length             | 3.43 in (8.7 cm) |
| Package 1 Weight             | 1.34 oz (38 g)   |

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

| Toxic Heavy Metal Free     |     |
|----------------------------|-----|
| Mercury Free               |     |
| Rohs Exemption Information | Yes |

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration  |
|--------------------------|--|
| Eu Rohs Directive        | Compliant<br>EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope)                                  |
| Environmental Disclosure | Product Environmental Profile  |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile      | End of Life Information  |