Product data sheet





MN undervoltage release, Compact NS 100 to 630, 220 VAC to 240 VAC 50/60 Hz, 208 VAC to 277 VAC 60 Hz

29407

Discontinued on: Jul 12, 2021

! Discontinued

Main

Range	ComPact
Range Of Product	NS100250 NS400630 DC NS100250 DC NR400630 NSF150250 NR100250 NR400600 NS400630 NS125E NSJ400600
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	208277 V AC 60 Hz 220240 V AC 50/60 Hz
Range Compatibility	ComPact ComPact NS ComPact Compact NB ComPact Compact NR ComPact Compact NSF ComPact Compact NSJ

Complementary

Operating Threshold	0.350.7 Un opening 0.85 Un closing
Response Time	< 50 ms
Supply Holding Power	< 5 VA
Auxiliary Connection Terminal	screw terminal 0.00 0.00 in² (0 1.5 mm²)

Ordering and shipping details

	· · · · · ·
Category	01103-H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
Gtin	3303430294078
Returnability	No
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	2.28 in (5.8 cm)
Package 1 Length	3.27 in (8.3 cm)
Package 1 Weight	4.30 oz (122 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration