



Price* : 303.00 USD



Main

Range	Multi 9
Product or component type	Miniature circuit-breaker
Product name	Multi 9 C60
Device short name	C60 UL489
Device application	Distribution
Number of protected poles	2
[In] rated current	8 A at 77 °F (25 °C)
Network type	AC DC
Trip unit technology	Thermal-magnetic
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary

System Voltage	125 V DC 240 V AC 440 V AC 415 V AC
Mounting mode	Clip-on
Poles description	2P
Interrupt Rating	Icu 6 kA at 440 V AC conforming to EN/IEC 60947-2 Icu 10 kA at 415 V AC conforming to EN/IEC 60947-2 Icu 20 kA at 240 V AC conforming to EN/IEC 60947-2 Icu 6 kA at 440 V AC conforming to GB 14048.2 Icu 10 kA at 415 V AC conforming to GB 14048.2 Icu 20 kA at 240 V AC conforming to GB 14048.2 AIR 10 kA at 240 V AC conforming to UL 489 AIR 10 kA at 125 V DC conforming to UL 489 Icu 10 kA at 125 V DC conforming to EN/IEC 60947-2 Icu 10 kA at 125 V DC conforming to GB 14048.2 AIR 10 kA at 240 V AC conforming to CSA C22.2 No 5.2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

AIR 10 kA at 125 V DC conforming to CSA C22.2 No 5.2

Network frequency	50/60 Hz
Curve code	C
Magnetic tripping limit	8.5 x In +/- 20% AC 12 x In +/- 20% DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting support	DIN rail
9 mm pitches	4
Height	4.84 in (123 mm)
Width	1.42 in (36 mm)
Depth	2.87 in (73 mm)
Product weight	0.49 lb(US) (0.22 kg)
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Ring terminal, top or bottom
Tightening torque	17.7 lbf.in (2 N.m) top or bottom

Environment

Standards	UL 489 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-2
Product certifications	UL CSA CCC IEC
IP degree of protection	IP40 modular enclosure conforming to IEC 60529 IP10 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Operating altitude	6561.68 ft (2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	00915 - C60N MINIATURE CIRCUIT BREAKER-UL489
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	0.560000000000000005
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0640 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
