# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications







# NEMA Control Relay, timing relay, 0 NO, one minute off delay, 230/250 VDC coil

8501XDO00XTD1V66

! Discontinued on: Dec 19, 2019

(!) Discontinued

### Main

Range	8501X	
Relay Type	Timing	
Product	Relay	
Current Rating	10 A AC 5 A DC	
Number Of Poles	0P	
Voltage Rating	250 V DC	

## Complementary

Coil Voltage	230/250 V DC
Coil Voltage Limints	Operational 0.81.1 Uc DC
Breaking Current	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 1.0 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301600 V DC inductive control circuit UL 508 4 A 125 V DC resistive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Making Current	60 A 120 V AC inductive control circuit UL 508 30 A 240 V AC inductive control circuit UL 508 15 A 480 V AC inductive control circuit UL 508 12 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301600 V DC inductive control circuit UL 508 4 A 125 V DC inductive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Time Delay Type	Off-delay
Time Delay Time	0.260 s
Coil Inrush In Watts	18 W
Coil Sealed Power In Watts	18 W
Device Operating Time	37 ms - pick-up 21 ms - drop-out
Contact Configuration	Without
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18AWG 12 copper

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Terminal Tightening Torque	Control circuit 9.0312.04 lbf.in (1.021.36 N.m) screw terminal
Mounting Type	Panel
Operating Temperature Range	-40160 °F (-4071 °C)
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	7.77 in (197.36 mm)

### **Environment**

Product Certifications CSA LR60905 class 3211 03
UL listed file E78403 CCN NKCR

# Ordering and shipping details

Category	21157-8501 XDO (DC)
Discount Schedule	CP2
Gtin	00785901340539
Returnability	No
Country Of Origin	MX

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov