


# 8501XO00XTE2V04

## Timing Relay - Three Minute On-Delay with 277VAC Coil with No Contacts



Price\* : 432.00 USD

8501XO00XTE2V04 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

### Main

Range	8501X
Relay Type	Timing
Product	Relay
Current Rating	10 A AC 5 A DC
Number of Poles	0P
Voltage Rating	600 V AC

### Complementary

Coil Voltage	277 V AC 60 Hz
Coil Voltage Limits	0.85...1.1 Uc operational AC 60 Hz
Breaking Current	6 A at: 120 V AC for inductive load control circuit per UL 508 3 A at: 240 V AC for inductive load control circuit per UL 508 1.5 A at: 480 V AC for inductive load control circuit per UL 508 1.2 A at: 600 V AC for inductive load control circuit per UL 508 10 A at: <= 600 V AC for resistive load control circuit per UL 508 1.1 A at: 125 V DC for inductive load control circuit per UL 508 0.55 A at: 250 V DC for inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for inductive load control circuit per UL 508 4 A at: 125 V DC for resistive load control circuit per UL 508 0.8 A at: 250 V DC for resistive load control circuit per UL 508
Making Current	60 A at: 120 V AC for inductive load control circuit per UL 508 30 A at: 240 V AC for inductive load control circuit per UL 508 15 A at: 480 V AC for inductive load control circuit per UL 508 12 A at: 600 V AC for inductive load control circuit per UL 508 10 A at: <= 600 V AC for resistive load control circuit per UL 508 1.1 A at: 125 V DC for inductive load control circuit per UL 508 0.55 A at: 250 V DC for inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for inductive load control circuit per UL 508 4 A at: 125 V DC for inductive load control circuit per UL 508 0.8 A at: 250 V DC for resistive load control circuit per UL 508
Time delay type	On-delay
Time Delay Time	5...180 s

Coil Inrush Power	148 VA at 60 Hz
Coil Sealed Power	At 60 Hz
Device Operating Time	15 ms pick-up 16 ms drop-out
Contact Configuration	Without
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	1.02...1.36 N.m control circuit screw terminal
Mounting Type	Panel
Operating Temperature Range	-40...160 °F
Height	3.5 in
Width	2.23 in
Depth	6.55 in

## Environment

Product certifications	UL listed file E78403 CCN NKCR CSA LR60905 class 3211 03
------------------------	---

## Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	3.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant <a href="#">Will be compliant</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------