# Product data sheet

Specifications



# Timing Relay - One Minute On-Delay with 24VAC Coil with No Contacts

8501XO00XTE1V01

() Discontinued on: Oct 11, 2019

() Discontinued

#### Main

Range	8501X	
Relay Type	Timing	
Product	Relay	
Current Rating	10 A AC 5 A DC	
Number Of Poles	0P	
Voltage Rating	600 V AC	

### Complementary

Coil Voltage	24 V AC 60 Hz
Coil Voltage Limints	Operational 0.851.1 Uc AC 60 Hz
Breaking Current	<ul> <li>6 A 120 V AC inductive control circuit UL 508</li> <li>3 A 240 V AC inductive control circuit UL 508</li> <li>1.5 A 480 V AC inductive control circuit UL 508</li> <li>1.2 A 600 V AC inductive control circuit UL 508</li> <li>10 A &lt;= 600 V AC resistive control circuit UL 508</li> <li>1.1 A 125 V DC inductive control circuit UL 508</li> <li>0.55 A 250 V DC inductive control circuit UL 508</li> <li>0.2 A 301600 V DC inductive control circuit UL 508</li> <li>4 A 125 V DC resistive control circuit UL 508</li> <li>0.8 A 250 V DC resistive control circuit UL 508</li> </ul>
Making Current	60 A 120 V AC inductive control circuit UL 508 30 A 240 V AC inductive control circuit UL 508 15 A 480 V AC inductive control circuit UL 508 12 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301600 V DC inductive control circuit UL 508 4 A 125 V DC inductive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Time Delay Type	On-delay
Time Delay Time	0.260 s
Coil Inrush Power	148 VA 60 Hz
Coil Sealed Power	23 VA 60 Hz
Device Operating Time	15 ms - pick-up 16 ms - drop-out
Contact Configuration	Without
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18AWG 12 copper

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Terminal Tightening Torque	Control circuit 9.0312.04 lbf.in (1.021.36 N.m) screw terminal
Mounting Type	Panel
Operating Temperature Range	-40160 °F (-4071 °C)
Height	3.5 in (88.90 mm)
Width	2.23 in (56.64 mm)
Depth	6.55 in (166.37 mm)

#### Environment

Product Certifications	CSA LR60905 class 3211 03
	UL listed file E78403 CCN NKCR

# Ordering and shipping details

Category	21158-8501 XO (AC)
Discount Schedule	CP2
Returnability	No
Country Of Origin	МХ

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov