


8501XO00XTE2V01

Timing Relay - Three Minute On-Delay with 24VAC Coil with No Contacts



Price* : 432.00 USD



8501XO00XTE2V01 has not been replaced. Please contact your customer care center for more information.

Main

Range	8501X
Relay Type	Timing
Product	Relay
Current Rating	10 A AC 5 A DC
Number of Poles	0P
Voltage Rating	600 V AC

Complementary

Coil Voltage	24 V AC 60 Hz
Coil Voltage Limits	0.85...1.1 Uc operational AC 60 Hz
Breaking Current	6 A at: 120 V AC for inductive load control circuit per UL 508 3 A at: 240 V AC for inductive load control circuit per UL 508 1.5 A at: 480 V AC for inductive load control circuit per UL 508 1.2 A at: 600 V AC for inductive load control circuit per UL 508 10 A at: <= 600 V AC for resistive load control circuit per UL 508 1.1 A at: 125 V DC for inductive load control circuit per UL 508 0.55 A at: 250 V DC for inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for inductive load control circuit per UL 508 4 A at: 125 V DC for resistive load control circuit per UL 508 0.8 A at: 250 V DC for resistive load control circuit per UL 508
Making Current	60 A at: 120 V AC for inductive load control circuit per UL 508 30 A at: 240 V AC for inductive load control circuit per UL 508 15 A at: 480 V AC for inductive load control circuit per UL 508 12 A at: 600 V AC for inductive load control circuit per UL 508 10 A at: <= 600 V AC for resistive load control circuit per UL 508 1.1 A at: 125 V DC for inductive load control circuit per UL 508 0.55 A at: 250 V DC for inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for inductive load control circuit per UL 508 4 A at: 125 V DC for inductive load control circuit per UL 508 0.8 A at: 250 V DC for resistive load control circuit per UL 508
Time delay type	On-delay
Time Delay Time	5...180 s

Coil Inrush Power	148 VA at 60 Hz
Coil Sealed Power	At 60 Hz
Device Operating Time	15 ms pick-up 16 ms drop-out
Contact Configuration	Without
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	1.02...1.36 N.m control circuit screw terminal
Mounting Type	Panel
Operating Temperature Range	-40...160 °F
Height	3.5 in
Width	2.23 in
Depth	6.55 in

Environment

Product certifications	UL listed file E78403 CCN NKCR CSA LR60905 class 3211 03
------------------------	---

Ordering and shipping details

Category	21158 - 8501 XO (AC)
Discount Schedule	CP2
Nbr. of units in pkg.	1
Package weight(Lbs)	3.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------