

Product data sheet

Specifications



Timing Relay - Three Minute On-Delay with 277VAC Coil with 2 NO Contacts

8501XO20XTE2V04

Discontinued on: Oct 11, 2019

Discontinued

Main

Range	8501X
Relay Type	Timing
Product	Relay
Current Rating	10 A AC 5 A DC
Number Of Poles	2P
Voltage Rating	600 V AC

Complementary

Coil Voltage	277 V AC 60 Hz
Coil Voltage Limints	Operational 0.85...1.1 Uc AC 60 Hz
Breaking Current	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301...600 V DC inductive control circuit UL 508 4 A 125 V DC resistive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Making Current	60 A 120 V AC inductive control circuit UL 508 30 A 240 V AC inductive control circuit UL 508 15 A 480 V AC inductive control circuit UL 508 12 A 600 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508 1.1 A 125 V DC inductive control circuit UL 508 0.55 A 250 V DC inductive control circuit UL 508 0.2 A 301...600 V DC inductive control circuit UL 508 4 A 125 V DC inductive control circuit UL 508 0.8 A 250 V DC resistive control circuit UL 508
Time Delay Type	On-delay
Time Delay Time	5...180 s
Coil Inrush Power	148 VA 60 Hz
Coil Sealed Power	23 VA 60 Hz
Device Operating Time	15 ms - pick-up 16 ms - drop-out
Contact Configuration	2 NO 2 standard contact cartridges
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Terminal Tightening Torque	Control circuit 9.03...12.04 lbf.in (1.02...1.36 N.m) screw terminal
Mounting Type	Panel
Operating Temperature Range	-40...160 °F (-40...71 °C)
Height	3.5 in (88.90 mm)
Width	2.23 in (56.64 mm)
Depth	6.55 in (166.37 mm)

Environment

Product Certifications	CSA LR60905 class 3211 03 UL listed file E78403 CCN NKCR
------------------------	---

Ordering and shipping details

Category	21158-8501 XO (AC)
Discount Schedule	CP2
Gtin	00785901869603
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------