

# 8536SAG12V90FF4T

Non-Reversing Starter Size 00, 3-Pole, Melting Alloy Overload, NEMA 1+Options



Price\*\* : 1,058.00 USD



8536SAG12V90FF4T has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	208 V AC 60 Hz primary circuit 24 V AC 60 Hz secondary circuit
Motor starter type	Non reversing
Current Rating	9 A
Number of Poles	3P
Number of Phases	3 phases
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Maximum Voltage Rating	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3
Electrical connection	Screw clamp terminals
NEMA size	00
Height	15.87 in (403 mm)
Depth	5.20 in (132 mm)
Width	6.34 in (161 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	NEMA

CSA  
UL listed

---

### Ordering and shipping details

---

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Package weight(Lbs)	20.40 lb(US) (9.253 kg)
Returnability	No

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---