

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 0, 2-Pole, Melting Alloy Overload, NEMA 1 +Options

8536SBG1V80CFF4P1TX10

Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Coil Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Control Circuit Type	Control circuit transformer
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO
Other Equipment	2 fuses (primary), 1 fuse (secondary)
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA NEMA UL Listed

### Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------