

8536SCW13V80F4P1P2T

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options

Price* : 2,156.00 USD



⚠ Discontinued

8536SCW13V80F4P1P2T has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Control Circuit Fusing	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	NEMA UL listed CSA

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
----------	--

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	40.050000000000004
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------