


8736SBA3V02SX1111

Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, NEMA 12 +Options



Price* : 2,010.00 USD



8736SBA3V02SX1111 has not been replaced. Please contact your customer care center for more information.

Main

Product	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Reversing
Motor type	Split phase
Number of Poles	3P
Phase	1 phase
Motor Wiring	4 wires
Line Rated Current	18 A
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Auxiliary Contacts	1 NO + 1 NC for reverse direction 1 NO + 1 NC for forward direction
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	13.74 in (349 mm)
Depth	7.76 in (197 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel
----------------	-----------------------------

Product certifications	CSA NEMA UL listed
------------------------	--------------------------

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	19.52
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------