

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 90A NEMA

8539SEW3V02S

Discontinued

Main

Contactor Application	Non-reversing
Device Short Name	S
Disconnecter Device Type	Thermal magnetic circuit breaker 90 A

Complementary

Depth	10.59 in (268.99 mm)
Device Mounting	Surface
Height	42 in (1066.80 mm)
Maximum Horse Power Rating	15 hp 200 V AC 20 hp 230 V AC 40 hp 460 V AC 50 hp 575 V AC
Nema Size	3
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker FAL
Net Weight	111 lb(US) (50.35 kg)
Width	15.25 in (387.35 mm)

Environment

Nema Degree Of Protection	NEMA 4/4X
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21218-8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	116.00 lb(US) (52.617 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------