

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 120 VAC coil, NEMA 1

8736SBG4V81CF4P1TX1111

Discontinued

Price\*: 2,840.00 USD

## Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

## Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Coil Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Control Circuit Type	Control circuit transformer
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC reverse 1 NO + 1 NC forward
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals
Height	11.89 in (302 mm)
Width	11.89 in (302 mm)
Depth	7.52 in (191 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	NEMA UL Listed CSA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Contractual warranty

Warranty	18 months
----------	-----------