

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 10,245.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	40 hp 200 V AC 3 phases 50 hp 230 V AC 3 phases 100 hp 575 V AC 3 phases 75 hp 460 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Thermal magnetic circuit breaker 200 A

Environment

Enclosure Type	NEMA 12 painted sheet steel and with external reset
NEMA size	4

Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	170
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------