

8736SBO10V02SX1010

Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, Vertical Open +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,412.00 USD



Main

Product	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Auxiliary Contacts	1 NO for reverse direction 1 NO for forward direction
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	11.54 in (293 mm)
Depth	5.31 in (135 mm)
Width	5.91 in (150 mm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Environment

Enclosure Type	Not rated (open device)
Orientation	Vertical
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	12
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------