

8736SBW14V02C14S

Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options



Price* : 2,484.00 USD



8736SBW14V02C14S has not been replaced. Please contact your customer care center for more information.

Main

Product	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (FORWARD-OFF-REVERSE)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	373 mm
Depth	7.8 in (198 mm)
Width	321 mm

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	NEMA UL listed

Ordering and shipping details

Category	21282 - 8702,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	38.560000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------