

# 8736SCA4V81F4T

## Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 12 +Options



Price\* : 1,971.00 USD



8736SCA4V81F4T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	27 A
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	13.74 in (349 mm)
Depth	7.76 in (197 mm)
Width	11.89 in (302 mm)

### Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	NEMA

UL listed  
CSA

---

### Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	23.580000000000002
Returnability	N
Country of origin	MX

---

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

---