

8736SCA4V84FF4T

Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 12 +Options



Price* : 2,285.00 USD



8736SCA4V84FF4T has not been replaced. Please contact your customer care center for more information.

Main

Product	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	27 A
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	1 fuse (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	13.74 in (349 mm)
Depth	7.76 in (197 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	NEMA

UL listed
CSA

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	23.710000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
