



Price* : 1,295.00 USD



8736SCG4V02S has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Control circuit	Separate control circuit
Device short name	S
Enclosure type	Enclosure standard environment indoor

Complementary

Rated current	27 A
System Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Depth	7.53 in
Device mounting	Surface
Electrical connection	Screw terminal
Height	11.88 in
Motor power hp	3 hp 230 V AC 2 hp 115 V AC
Motor starter type	Reversing
NEMA size	1
Network number of phases	1 phase
Number of poles	3
Number of thermal units required	1
Permissible voltage	<= 600 V AC
Product weight	17 lb(US)
Short-circuit protection	5000 A AIR
Thermal overload type	Melting alloy
Width	11.88 in

Environment

NEMA degree of protection	NEMA 1
Product certifications	NEMA UL listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	25.359999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------