

Product data sheet

Characteristics

8736SCG6V08

Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,295.00 USD



Main

Product	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Reversing
Motor type	Split phase
Number of Poles	3P
Phase	1 phase
Motor Wiring	4 wires
Line Rated Current	27 A
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	11.89 in (302 mm)
Depth	7.52 in (191 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA

NEMA
UL listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	23.600000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------