


Product data sheet

Specifications



NEMA Starter, Type S, reversing, horizontal, Size 00, 9A, 2 HP at 575 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic SSOLR, 208 VAC coil, open

8736SAQ16V08H30

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10/20
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Sccr	Circuit-breaker 70 A maximum: 100 kA at 480 V AC Fuse J 60 A maximum: 100 kA at 600 V AC Fuse T 60 A maximum: 100 kA at 600 V AC Fuse RK1 60 A maximum: 100 kA at 600 V AC Fuse RK5 60 A maximum: 100 kA at 600 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	6.91 in (175.51 mm)
Width	7.13 in (181.10 mm)
Depth	5.31 in (134.87 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.93 in (17.6 cm)
Package 1 Width	7.13 in (18.1 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	8.00 lb(US) (3.629 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant