

# Product data sheet

## Characteristics


# 8736SDA1V06

## Reversing Starter Size 2, 3-Pole, Melting Alloy Overload, NEMA 12

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 3,011.00 USD



### Main

Product	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	45 A
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	2
Height	15.98 in (406 mm)
Depth	7.87 in (200 mm)
Width	14.88 in (378 mm)

### Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA

NEMA  
UL listed

### Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901125570
Nbr. of units in pkg.	1
Package weight(Lbs)	20.469999999999999
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------