

# Product data sheet

Specifications



## Two Speed Starter, Size 3, 3-Pole, Melting Alloy OLR, Open, 120/110V 60/50Hz

8810SEO12V02S

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 8,527.00 USD

### Main

Product Or Component Type	Starter
Range Of Product	Type S

### Complementary

Control Circuit	Separate control circuit
Control Type	Without
Nema Degree Of Protection	Not rated (open device)
Auxiliary Contact Composition	Without
Maximum Horse Power Rating	25 hp 200 V AC, 3 phase 30 hp 230 V AC, 3 phase 50 hp 380 V AC, 3 phase 50 hp 460/575 V AC, 3 phase
Poles Description	3P
Maximum Operating Voltage	600 V AC
Nema Size	3
[Uc] Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Local Signalling	Without pilot light
Motor Starter Type	2 speed
Electrical Connection	Lugs
Thermal Overload Type	melting alloy
Number Of Thermal Units Required	6
Asynchronous Motor Control Profile	Constant/variable torque
Maximum Operating Current	90 A

### Environment

Product Certifications	UL listed file E78351 CCN NLDX CSA LR60905 class 3211 04
------------------------	---

### Ordering and shipping details

Category	US10CP121302
Discount Schedule	0CP1
Gtin	785901890508

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20.32 in (51.613 cm)
Package 1 Width	28.26 in (71.775 cm)
Package 1 Length	34.29 in (87.097 cm)
Package 1 Weight	80.20 lb(US) (36.377 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>