Product data sheet

Specification





Illuminated push-button, Harmony 9001K, metal, projecting, white, 30mm, spring return, 24-28V, 1 C/O

9001K2L35WH13



Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001K |
|---------------------------------|----------------------------|
| Product Or Component Type | Illuminated push-button |
| Device Short Name | 9001K |
| Type Of Operator | spring return |
| Operator Profile | White projecting, unmarked |
| Operator Additional Information | Without quard |

Complementary

| Bezel Material | Metal |
|--|---|
| Mounting Diameter | 1.18 in (30 mm) |
| Shape Of Signaling Unit Head | Octagonal |
| Light Source | incandescent |
| Light Source | Incandescent bulb |
| Bulb Base | BA 9s |
| Light Block Supply | Direct |
| [Us] Rated Supply Voltage | 2428 V AC/DC |
| Contacts Type And Composition | 1 C/O |
| Connections - Terminals | Screw clamp terminals 1 x 0.222 x 1.5 mm² IEC 60947-1 |
| Tightening Torque | 7.08 lbf.in (0.8 N.m) IEC 60947-1 |
| Shape Of Screw Head | Cross slotted |
| Mechanical Durability | 5000000 cycles |
| Operating Position | Any position |
| [Ui] Rated Insulation Voltage | 250 V 3)IEC 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 2.5 kV IEC 60947-1 |
| Contacts Material | Silver alloy contacts |
| Contact Operation | Standard |
| Positive Opening | Without |
| Short-Circuit Protection | 10 A cartridge fuse IEC 60947-5-1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



| [Ith] Conventional Free Air Thermal Current | 10 A |
|--|--|
| [Icm] Rated Short-Circuit Making Capacity | 12 kA 600 V AC-15, 7200 VA 15 kA 480 V AC-15, 7200 VA 30 kA 240 V AC-15, 7200 VA 60 kA 120 V AC-15, 7200 VA |
| Rated Breaking Capacity | 1.2 kA 600 V AC-15, 720 VA 1.5 kA 480 V AC-15, 720 VA 3 kA 240 V AC-15, 720 VA 6 kA 120 V AC-15, 720 VA 0.1 kA 600 V DC-13 0.27 kA 250 V DC-13 0.55 kA 125 V DC-13 |
| Cad Overall Width | 2.13 in (54 mm) |
| Cad Overall Height | 1.65 in (42 mm) |
| Cad Overall Depth | 4.06 in (103 mm) |
| Terminals Description Iso N°1 | (13-14-11-12)OF |
| Net Weight | 0.37 lb(US) (0.166 kg) |
| Device Presentation | Complete product |
| Cap/Operator Or Lens Colour | White |
| [Us] Rated Supply Voltage | 2428 V |
| Light Block Supply | Full voltage |
| Operator Profile | Projecting |
| Type Of Operator | Spring return |
| Size | 30 mm |

Environment

| Standards | EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-5-1 JIS C 4520 UL 508 CSA C22.2 No 14 |
|---------------------------------------|--|
| Product Certifications | NEMA UL 508 |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Vibration Resistance | 7 gn 2500 Hz)IEC 60068-2-6 |
| Shock Resistance | 50 gn IEC 60068-2-27 |
| Overvoltage Category | Class II IEC 61140 |
| Ip Degree Of Protection | IP66 IEC 60529 |
| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4 |

Ordering and shipping details

Category US10CS121426

| Discount Schedule | 0CS1 |
|-------------------|--------------|
| Gtin | 785901831334 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.90 in (4.826 cm) |
| Package 1 Width | 2.30 in (5.842 cm) |
| Package 1 Length | 4.50 in (11.43 cm) |
| Package 1 Weight | 8.00 oz (226.796 g) |

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

| Reach Regulation | REACh Declaration | | | | |
|---------------------------|---|--|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | | |
| China Rohs Regulation | China RoHS declaration | | | | |
| Environmental Disclosure | Product Environmental Profile | | | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | | | | |
| Circularity Profile | No need of specific recycling operations | | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | | |

Dimensions Drawings

Dimensions




 \boldsymbol{e} panel thickness: 1 to 6 mm/ 0.04 to 0.24 in.

9001K2L35WH13

Mounting and Clearance

Contact Block Mounting Position


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Panel Cut-Out

Clearance



| Legend plate | a min. | | b min. | |
|--------------|--------|------|--------|------|
| | mm | in. | mm | in. |
| 9001KN2•• | 57.2 | 2.25 | 44.5 | 1.75 |
| 9001KN3•• | 57.2 | 2.25 | 50.8 | 2.00 |

Individual Cut-outs Details

2 alternatives

