

# 8736SBW14V81A1F4T

## Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options



Price\* : 2,768.00 USD



8736SBW14V81A1F4T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	3 momentary push-buttons (FORWARD-REVERSE-STOP)
Control Circuit Fusing	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	373 mm
Depth	7.8 in (198 mm)
Width	321 mm

### Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA

NEMA  
UL listed

---

### Ordering and shipping details

Category	21282 - 8702,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	42.530000000000001
Returnability	N
Country of origin	MX

---

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

---