Product data sheet

Specifications







Contactor, Type L, multipole lighting, power pole, 30A, 2 pole, 2 normally open contacts, 600V, right side mount

8903L3R

Product availability: Stock - Normally stocked in distribution facility

Price*: 171.00 USD

Main

Product Or Component Type	Auxiliary Contact Module
Range Of Product	8903L
Complementary	
Electrical Connection	Screw-clamp terminals
Height	3.03 in (77 mm)
Depth	1.97 in (50 mm)
Width	2.52 in (64 mm)

Environment

Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121321	
Discount Schedule	0CP1	
Gtin	785901620259	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	8.32 oz (235.868 g)

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations