

Product data sheet

Specifications

SQUARE D



joystick controller - Ø 30 - 5
positions spring return - without
contact

9001K35H13

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Joystick controller
Device Short Name	9001K
Sale Per Indivisible Quantity	1
Type Of Operator	spring return
Operator Profile	80 mm long operating shaft

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.82 lb(US) (0.372 kg)
Operating Position	Any position
Shape Of Signaling Unit Head	Octagonal
Operator Position Information	5 positions
Contacts Type And Composition	Without contact block
Device Presentation	Basic element

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Overvoltage Category	II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508 EN/IEC 60947-5-4 EN/IEC 60947-1 JIS C 852 CSA C22.2 No 14 JIS C8201-5-1 EN/IEC 60947-5-1 JIS C8201-1
Product Certifications	NEMA UL 508
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901824510
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------