

# Product data sheet

Specifications

SQUARE D



## PUSH BUTTON - 600 VAC 10 A - Ø30 - Type K

9001K3L38LLH5

Discontinued on: Oct 11, 2019

Product availability: Non-Stock - Not normally stocked in distribution facility

Discontinued

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Illuminated push-button
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	Blue flush, unmarked
Operator Additional Information	Extended metallic guard

### Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Light Source	Blue LED
Bulb Base	BA 9s
Light Block Supply	Direct
[Us] Rated Supply Voltage	120 V AC/DC
Contacts Type And Composition	1 NO
Connections - Terminals	Screw clamp terminals 1 x 0.22...2 x 1.5 mm² IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1
Mechanical Durability	5000000 cycles
Operating Position	Any position
Contacts Material	Silver alloy contacts
Contact Operation	Standard
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A
[Icm] Rated Short-Circuit Making Capacity	12 kA
Device Presentation	Complete product

### Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	JIS C 4520 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1 UL 508 EN/IEC 60947-5-4 EN/IEC 60947-1
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	00785901748861
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------